

# **OPTICAL POWER METER 3664**

Optical/Telecom Measurement



From Blue-Ray, High Definition DVD to Near-Infrared Rays

**An Advanced Optical Power Meter to Meet** 



# A Truly Flexible Instrument Catering to Applications in R&D,

Optical Power Meter 3664 serves as a convenient tool for the R&D, manufacture and maintenance of equipment that incorporate laser light sources, such as DVD recorders, CD drives, copiers, and laser printers. With the addition of the Optical Sensors 9743 and 9743-10 specifically designed for blue-violet optical rays that have low dependency on the incidence angle and flat wave sensitivity characteristics over its 405nm bandwidth, the 3664 also proves to be a powerful instrument for inspecting next generation optical pickup drive devices.

## Four Sensors to Accommodate All Types of Testing Needs

Choose from 4 different optical sensors according to wavelength and sensor structure to aptly meet your application requirements.

## ■ Two Different Bandwidths

## Blue-violet Optical Sensor 9743/9743-10

Incorporated with characteristics that are ideal for measuring blue-violet lasers found in high-definition DVDs, Models 9743 and 9743-10 offer the following features:

- Planar wavelength sensitivity characteristics at the 405 nm bandwidth
- Low Incident Angle Dependency and Low Reflection





## ■ Two Different Styles





# Production and Maintenance of Laser- and LED-Dependent Equipment

## **Powerful Features**

## **■** Superior cost performance

Guaranteed accuracy of  $\pm 5\%$ , ideal for the production and testing of optical pickup devices (in combination with the Optical Sensor 9742/9742-10/9743/9743-10) Scaling functionality and USB compatibility all for one reasonable price.

## ■ Scaling

Adjust for sensitivity at the wavelength level, and easily integrate the 3664 into an inspection standard device.

## Wavelength setting resolution up to 1 nm

Up to 10 wavelength memory presets can be configured, including the defaults for each optical sensor. The default wavelengths for each optional sensor are already stored in memory. Add up to 6 more custom wavelengths and call them up simply by pressing the  $\lambda$  key.

## **■ MAX/MIN/AVE measurement**

Display maximum, minimum, and averages, as well as make relative measurements.



## 2 Power settings

Compatible to both DC power and AC power. Choose a power method to suit your application.

### ■ Relative measurement

Display measurements as relative values, i.e., the difference from a set reference value. Load reference values from a measured value or define according to your requirements.

# ■ Upload data through the USB interface

Program your PC to download captured data, configure and even control the 3664 through the USB interface. (USB driver software included)

## **Specifications**

Accuracy: 23°±5°C (73°±9°F), less than 80% rh, One year accuracy guarantee

## ■ OPTICAL POWER METER 3664 Specifications

Optical power measurement	Units W/dBm
Range	Auto (manual settings available)
Accuracy	$\pm$ 0.7 % ( $\pm$ 5 % when used with optional light sensor)
Calibration	Resolution of 1 nm, automatic calibration of sensor, up to 10
wavelength	wavelength presets available (including defaults for each sensor)
Scaling	Configurable for each wavelength
	Displays a measured value compared with a reference value
Optical loss	(Displayed value = measurement – reference)
measurement	* Reference value can be based on a measurement, or input manually
Diamlari	* Settings range: 0.001 nW to 1.9999 W (-90.00 dBm to 33.00 dBm)
Display	4 ½ digits, up to 19999. Display resolution: 0.01 dBm/0.01 dB
Measurement display	Units: nW/µW/mW/dBm/dB
Wavelength display	4 digits, unit: nm
Display refresh rate	Approx. 330 ms
MAX/MIN display	Displays MAX/MIN during measurement
AVE display	Moving average, average count configurable from 2 to 100
Analog Output	According to optional Optical Sensor in use
	9742/9742-10: Approx. 1V at sensor correction input
	9743/9743-10: Approx. 0.7V at sensor correction input
Output resistance	
Output connector	,
Interface	USB Ver1.1
	Output of measurement data, configuration and control supported
Included features	Auto power save, configuration backup, battery check
Applicable	Safety standard: EN61010-1
standards	EMC:EN61326, EM61000-3-2, EM61000-3-3
Power	LR6 (AA) Alkaline battery X 4, AC adapter (9445-02/9445-03)
Max. rated power	1.6 VA
Operating time	Approx. 60 hours (when using battery, continuous use with 9742 optical sensor as correction input)
Operating conditions	0°C to -40°C (32°F to 104°F), up to 80 % rh (no condensation)
Storage conditions	-10°C to 50°C (14°F to 122°F), up to 80 % rh (no condensation)
Operating environment	Indoor, up to elevation of 2000 meters (6562 ft)
Dimensions and mass	Approx. 85WX160HX35Dmm (3.35WX6.30HX1.38 D inches) (excluding protrusions), Approx. 270g (9.5 oz.) (without batteries)


## ■ OPTICAL SENSOR Specifications

9742/9742-10

Maggurad wavalanath	
ivicasureu wavelerigiri	320 to 1100 nm
Measured power	-59 dBm to +17 dBm (correction wavelength)
Maximum rated value	50 mW (+17 dBm) (under direct lighting)
Receiving element	Si Photo diode
Receptor size	Approx. 9.6 mm × 9.6 mm (0.38" × 0.38")
Accuracy	$\pm4.3~\%~(\pm5~\%$ when used with OPTICAL POWER METER 3664) [Correction conditions] correction wavelength 633 nm, correction power 100 $\mu$ W, when ø approx. 2 mm (0.08") parallel beam strikes perpendicular to center of optical sensor, CW light
Wavelength configuration defaults	633 nm, 635 nm, 650 nm, 780 nm
Operating conditions	0 °C to -40 °C (32°F to 104°F), up to 80 % rh (no condensation)
Storage conditions	-10 °C to 50 °C (14°F to 122°F), up to 80 % rh (no condensation)
Operating environment	Indoor, elevation up to 2000 meters (6562 ft)
Mass	Approx. 100 g (3.5 oz.)
9743/9743-10	
Measured wavelength	
	-50 dBm to + 20 dBm (correction wavelength)
Maximum rated value	100 mW (+20 dBm) (under direct lighting)
	, , , , , , , , , , , , , , , , , , , ,
Receiving element	Si Photo diode
	Si Photo diode Approx. 10 mm × 10 mm ( 0.39" × 0.39")
Receiving element	
Receiving element Receptor size	Approx. 10 mm $\times$ 10 mm (0.39" $\times$ 0.39") $\pm 4.3\%$ ( $\pm 5\%$ when used with OPTICAL POWER METER 3664) [Correction conditions] correction wavelength 405 nm (Using a $\pm 405 \pm 5$ nm wavelength as the reference wavelength), correction power 100 $\mu$ W, when $\pm$ approx. 1.5 mm (0.06") parallel
Receiving element Receptor size Accuracy	Approx. 10 mm $\times$ 10 mm (0.39" $\times$ 0.39") $\pm 4.3\%$ ( $\pm 5\%$ when used with OPTICAL POWER METER 3664) [Correction conditions] correction wavelength 405 nm (Using a $405 \pm 5$ nm wavelength as the reference wavelength), correction power 100 $\mu$ W, when ø approx. 1.5 mm (0.06") parallel beam strikes perpendicular to center of optical sensor 400 nm, 403 nm, 405 nm, 408 nm 0 °C to -40 °C (32°F to $104$ °F), up to 80 % rh (no condensation)
Receiving element Receptor size Accuracy Wavelength configuration defaults	Approx. 10 mm $\times$ 10 mm ( $0.39$ " $\times$ 0.39") $\pm 4.3\%$ ( $\pm 5\%$ when used with OPTICAL POWER METER 3664) [Correction conditions] correction wavelength 405 nm (Using a $405\pm 5$ nm wavelength as the reference wavelength), correction power 100 $\mu$ W, when ø approx. 1.5 mm (0.06") parallel beam strikes perpendicular to center of optical sensor 400 nm, 403 nm, 405 nm, 408 nm 0 °C to -40 °C (32°F to 104°F), up to 80 % rh (no condensation)
Receiving element Receptor size Accuracy  Wavelength configuration defaults Operating conditions Storage conditions	Approx. 10 mm $\times$ 10 mm (0.39" $\times$ 0.39") $\pm 4.3\%$ ( $\pm 5\%$ when used with OPTICAL POWER METER 3664) [Correction conditions] correction wavelength 405 nm (Using a $405 \pm 5$ nm wavelength as the reference wavelength), correction power 100 $\mu$ W, when ø approx. 1.5 mm (0.06") parallel beam strikes perpendicular to center of optical sensor 400 nm, 403 nm, 405 nm, 408 nm 0 °C to -40 °C (32°F to $104$ °F), up to 80 % rh (no condensation)

Please refer to the external diagrams depicted on the next page for the exact dimensions of the optical sensors.

## **OPTICAL SENSOR exterior view**





## ■ 3664 OPTICAL POWER METER

#### Accessories:

AC ADAPTER 9445-02 (UL) (1) or AC ADAPTER 9445-03 (CEE) (1), OUTPUT CORD 9094 (1), USB CABLE (1), USB Driver CD-R (1), Strap (1), Batteries (AAx4)

The **POWER METER 3664** must be used in conjunction with either the 9742 or 9742-10 or 9743 or 9743-10 OPTICAL SENSOR, sold separately.





Optical Power Meters installed with firmware version 1.01 or earlier must be updated to support compatibility with the new Optical Sensor 9743/9743-10

When using Model 9743/9743-10 with an earlier version of Model 3664, upon connecting the sensor to the optical power meter and turning on the power, "Err1" will be displayed.

To update your Model 3664, please visit our website at www.hioki.com to download the latest firmware, "HIOKI 3664 Setup Utility" and refer to the instructions provided to learn how to set up the proprietary data for the new optical sensor.

### HIOKI E.E. CORPORATION

## **HEAD OFFICE:**

81 Koizumi, Ueda, Nagano, 386-1192, Japan TEL +81-268-28-0562 / FAX +81-268-28-0568 E-mail: os-com@hioki.co.jp

### HIOKI USA CORPORATION:

6 Corporate Drive, Cranbury, NJ 08512 USA TEL +1-609-409-9109 / FAX +1-609-409-9108 E-mail: hioki@hiokiusa.com

HIOKI (Shanghai) Sales & Trading Co., Ltd.:
1904 Shanghai Times Square Office, 93 Huai Hai Zhong Road
Shanghai, P.R.China POSTCODE: 200021 TEL +86-21-6391-0090/0092 FAX +86-21-6391-0360 E-mail: info-sh@hioki.cn

## Beijing Office:

Beijing Griectown, 58 Dong San Huan Nan Road Beijing, P.R.China POSTCODE: 100022 TEL +86-10-5867-4080/4081 FAX +86-10-5867-4090 F-mail· info-bi@hioki cn

### Guangzhou Office:

Room 303, Profit Plaza, No.76, West Huangpu Road Guangzhou, P.R.China POSTCODE: 510623 TEL +86-20-38392673/2676 FAX +86-20-38392679 E-mail: info-gz@hioki.cn